


B 193
RIPP LOCK® self-locking nuts

With flange and tothing

Steel | bright | Cr(VI)-free | Metric thread

Further information: Strength class 10



Diameter (d)	d _a		d _c		h			m		
	min.	max.	min.	max.	nominal size	min.	max.	nominal size	min.	max.
M5	5	5.75	10.80	11.20	0.8	0.6	1.0	4.3	4.06	4.54
M6	6	6.75	13.75	14.25	0.9	0.7	1.1	5.5	5.26	5.74
M8	8	8.75	17.70	18.20	1.2	1.0	1.4	7.0	6.71	7.29
M10	10	10.80	20.40	21.00	1.6	1.4	1.8	8.5	8.21	8.79
M12	12	13.00	23.30	24.00	1.6	1.4	1.8	10.0	9.71	10.29
M16	16	17.30	30.20	31.00	1.8	1.6	2.0	14.0	13.65	14.35

Diameter (d)	e	r	s		Pitch (P)	Tool size
	min.	max.	min.	max.		
M5	8.87	0.30	7.78	8	0.80	SW 8
M6	11.05	0.36	9.78	10	1.00	SW 10
M8	14.38	0.48	12.73	13	1.25	SW 13
M10	16.64	0.60	14.73	15	1.50	SW 15
M12	18.90	0.72	16.73	17	1.75	SW 17
M16	24.49	0.96	21.67	22	2.00	SW 22

All technical data refer to the measure mm

