


DIN 128
Spring washers

Form A: curved

Stainless steel A4 | Cr(VI)-free

Further information: Norm has been withdrawn without replacement | also suitable for left-handed threads



$C < s_{min}$

Diameter (d)	b		d ₁		d ₂ max.	h		r	s			
	nominal size	min.	max.	min.		max.	min.		max.	nominal size	min.	max.
3	1.3	1.20	1.40	3.1	3.4	6.2	1.10	1.30	0.1	0.7	0.60	0.80
3.5	1.3	1.20	1.40	3.6	3.9	6.7	1.10	1.30	0.1	0.7	0.60	0.80
4	1.5	1.40	1.60	4.1	4.4	7.6	1.20	1.40	0.2	0.8	0.70	0.90
5	1.8	1.70	1.90	5.1	5.4	9.2	1.50	1.70	0.2	1.0	0.90	1.10
6	2.5	2.35	2.65	6.1	6.5	11.8	2.00	2.20	0.3	1.3	1.20	1.40
8	3.0	2.85	3.15	8.1	8.5	14.8	2.45	2.75	0.5	1.6	1.50	1.70
10	3.5	3.30	3.70	10.2	10.7	18.1	2.85	3.15	0.5	1.8	1.70	1.90
12	4.0	3.80	4.20	12.2	12.7	21.1	3.35	3.65	1.0	2.1	1.95	2.25
14	4.5	4.30	4.70	14.2	14.7	24.1	3.90	4.30	1.0	2.4	2.25	2.55
16	5.0	4.80	5.20	16.2	17.0	27.4	4.50	5.10	1.0	2.8	2.65	2.95
18	5.0	4.80	5.20	18.2	19.0	29.4	4.50	5.10	1.0	2.8	2.65	2.95
20	6.0	5.80	6.20	20.2	21.2	33.6	5.10	5.90	1.0	3.2	3.00	3.40
22	6.0	5.80	6.20	22.5	23.5	35.9	5.10	5.90	1.0	3.2	3.00	3.40
24	7.0	6.75	7.25	24.5	25.5	40.0	6.50	7.50	1.6	4.0	3.80	4.20

All technical data refer to the measure mm

