DIN 1440 similar to ISO 8738


Washers

Medium version | for studs

Stainless steel A2 | Cr(VI)-free

Further information: DIN standard has been withdrawn





| Diameter | d ₁ | d_2 | s |
|----------|----------------|--------------|--------------|
| (d) | nominal size | nominal size | nominal size |
| 3 | 3 | 6 | 0.8 |
| 4 | 4 | 8 | 0.8 |
| 5 | 5 | 10 | 0.8 |
| 6 | 6 | 12 | 1.6 |
| 7 | 7 | 14 | 1.6 |
| 8 | 8 | 16 | 2.0 |
| 10 | 10 | 20 | 2.5 |
| 12 | 12 | 25 | 3.0 |
| 13 | 13 | 25 | 3.0 |
| 14 | 14 | 28 | 3.0 |
| 16 | 16 | 28 | 3.0 |
| 18 | 18 | 30 | 4.0 |
| 20 | 20 | 32 | 4.0 |
| 22 | 22 | 34 | 4.0 |
| 23 | 23 | 36 | 4.0 |
| 25 | 25 | 40 | 4.0 |
| 27 | 27 | 40 | 5.0 |
| 28 | 28 | 42 | 5.0 |
| 30 | 30 | 45 | 5.0 |
| 32 | 32 | 50 | 5.0 |
| 33 | 33 | 50 | 5.0 |
| 36 | 36 | 52 | 6.0 |
| 40 | 40 | 58 | 6.0 |