DIN 7984


Cylinder screws


Hexagon socket | low head

Steel 08.8 | zinc-plated, thick-film passivated (VZD) | Cr(VI)-free | Metric thread

Further information: Due to their head geometry, these screws are limited in their load bearing capacity, see DIN EN ISO 898-1







Diameter	b			da	d _k		d _s		k	
(d)	I up to 125	I up to 200	I longer than 200	max.	min.	max.	min.	max.	min.	max.
M8	22	28	_	9.2	12.73	13	7.78	8	4.82	5
M16	38	44	57	17.7	23.67	24	15.73	16	8.78	9
M24	54	60	73	26.4	35.61	36	23.67	24	12.73	13

Diameter	е	r	s		Pitch	t			Tool	
(d)	min.	min.	nominal size	min.	max.	(P)	nominal size	max.	min.	size
M8	5.72	0.4	5	5.02	5.12	1.25	3.8	3.95	3.65	SW 5
M16	13.72	0.6	12	12.03	12.21	2.00	5.5	5.65	5.35	SW 12
M24	19.44	0.8	17	17.05	17.23	3.00	8.0	8.18	7.82	SW 17

Length (I)							
nominal size	min.	max.					
25	24.58	25.42					
35	34.50	35.50					
55	54.50	55.50					

Diameter	Le	Length (I)				
(d)	25	35	55			
M8	•					
M16						
M24			•			

 \bullet Combinations available in the eShop | Other sizes on request



All technical data refer to the measure mm