

DIN 7985 similar to ISO 7045

Pan head screws

Cross-slot phillips

Steel 4.8 | zinc-plated, thick-film passivated (VZD) | Cr(VI)-free | Metric thread
 Further information: DIN-standard has been withdrawn | changed head height



Diameter (d)	a	d _a	d _k		k			rf	r	Pitch (P)	v	Tool size
	max.	max.	min.	max.	nominal size	min.	max.		max.			
M2.5	0.9	3.1	4.70	5	2.0	1.88	2.12	5	0.1	0.45	1.3	H1
M4	1.4	4.7	7.64	8	3.1	2.95	3.25	8	0.2	0.70	2.0	H2
M5	1.6	5.7	9.64	10	3.8	3.65	3.95	10	0.2	0.80	2.5	H2
M8	2.5	9.2	15.57	16	6.0	5.85	6.15	16	0.4	1.25	3.7	H4

nominal size	Length (l)	
	min.	max.
6	5.75	6.25
8	7.70	8.30

nominal size	Length (l)	
	min.	max.
10	9.70	10.30
20	19.60	20.40
30	29.60	30.40

Diameter (d)	Length (l)				
	6	8	10	20	30
M2.5	●	●			
M4		●			
M5			●	●	
M8			●		

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

