

ISO 7380-1

Round head screws

Halbrundkopf | Torx

Steel 10.9 | zinc-plated | Cr(VI)-free | Metric thread



Diameter (d)	a		d _a max.	d _k		k		e min.	r min.	s			Pitch (P)	t	
	min.	max.		min.	max.	min.	max.			nominal size	min.	max.		max.	min.
4	0.70	1.4	4.7	7.24	7.6	1.95	2.20	2.87	0.20	2.5	2.52	2.58	0.70	1.66	1.27
5	0.80	1.6	5.7	9.14	9.5	2.50	2.75	3.44	0.20	3.0	3.02	3.08	0.80	1.91	1.52
6	1.00	2.0	6.8	10.07	10.5	3.00	3.30	4.58	0.25	4.0	4.02	4.10	1.00	2.42	1.90
8	1.25	2.5	9.2	13.57	14.0	4.10	4.40	5.72	0.40	5.0	5.02	5.14	1.25	3.05	2.55

Length (l)	
nominal size	
6	
8	
10	
12	
16	
20	

Length (l)	
nominal size	
25	
40	

Diameter (d)	Length (l)							
	6	8	10	12	16	20	25	40
4	●	●	●	●	●	●		
5		●	●	●	●	●	●	●
6					●	●	●	
8						●	●	

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

