

**ISO 7380-2**

**Round head screws**

Halbrundkopf mit Flansch | Torx

Steel 10.9 | zinc-plated | Cr(VI)-free | Metric thread



Diameter (d)	b nominal size	c		d <sub>a</sub> max.	d <sub>c</sub>		d <sub>k</sub>		d <sub>s</sub>	
		min.	max.		min.	max.	min.	max.	min.	max.
4	20	0.65	0.8	4.7	8.82	9.4	6.8	7.2	3.82	4
5	22	0.80	1.0	5.7	11.10	11.8	8.4	8.8	4.82	5
6	24	1.00	1.2	6.8	12.90	13.6	9.6	10.0	5.82	6
8	28	1.25	1.5	9.2	17.10	17.8	12.8	13.2	7.78	8
10	32	1.70	2.0	11.2	21.06	21.9	16.1	16.5	9.78	10

Diameter (d)	d <sub>w</sub> min.	k		e min.	s			Pitch (P)	t min.	w min.
		min.	max.		nominal size	min.	max.			
4	8.24	1.95	2.20	2.87	2.5	2.52	2.58	0.70	1.30	0.30
5	10.40	2.50	2.75	3.44	5.0	5.02	5.14	0.80	1.56	0.38
6	12.20	3.00	3.30	4.58	4.0	4.02	4.10	1.00	-	0.74
8	16.40	4.10	4.40	5.72	5.0	5.02	5.14	1.25	-	1.05
10	20.22	5.20	5.50	6.86	6.0	6.02	6.14	1.50	-	1.45

Length (l)	
nominal size	
6	
8	
10	
12	
16	
20	

Length (l)	
nominal size	
25	
30	
35	
40	
50	

Diameter (d)	Length (l)										
	6	8	10	12	16	20	25	30	35	40	50
4	●	●	●	●	●	●					
5			●	●	●	●	●	●	●	●	●
6				●	●	●	●	●			
8				●	●	●	●	●	●	●	
10						●	●				

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

