
Steel | Type 1230 | standard

Advantages:

- No tapping
- Quick, cost-effective installation
- Chipping-free installation in smooth mounting holes
- High-strength threads in light metals
- High-strength threads in thermoplastic and thermoset components** after moulding of components
- Suitable for one-sided accessibility of the installation point
- For screwed connections that can be detached as often as required
- For installation on finished surfaces





Diameter	Article number	a	Length (I)	l ₁	Outer	L	L2
(d)		nominal size	nominal size		diameter (d2)	min.	min.
M4	12300040063	2.0	10.5	6.3	6.5	11.8	6.3
M5	12300050082	2.5	13.5	8.2	7.5	15.2	8.2
M6	12300060098	3.0	16.0	9.8	9	18.8	9.8
M8	12300080115	4.0	19.0	11.5	12	21.0	11.5

^{**} Particularly test this insert for suitability for plastics susceptible to stress cracks (e.g. PC, PPO).