# All technical data refer to the measure mm

## RIVKLE® Hydraulic/pneumatic setting tool

This high-speed robust stroke-controlled setting tool is used to set RIVKLE® Standard blind rivet nuts made of aluminium (M3-M12), steel (M3-M12) and stainless steel (M3-M10).

#### **Delivery scope:**

- Basic tool
- Operating instructions
- Practical case for storage and transport


Threaded mandrels and anvils are not included in the delivery scope and must be ordered separately.


Technical information can be found on the last page.



(d)	Diameter	Article number	Weight
(u) g	(d)		g


M 3 - M 12 23615501000 2600






#### **Grip range**

Defines the range of total thickness of the customers part (even if it consists of more than one layer)




### Hole geometry

If round -> diameter If hexagonal -> wigth across flats



Difference of total length before and after installation



\*in accordance to chosen RIVKLE®\*

