


B 52035  
QUICK FLOW® Plus thin sheet screw

Form C | button head | hexalobular drive

Steel | zinc-plated, thick-film passivated (VZD) | Cr(VI)-free | self-tapping thread  
Incl. 3 suitable bits per PU



Diameter (d)	a max.	min.	d <sub>k</sub> max.	e nominal size	k max.	Pitch (P)	max.	t min.	Tool size
4	1	7.64	8	7	3.1	1.4	1.66	1.27	TX 20

Length (l) nominal size
19

Diameter (d)	Length (l)
4	19

- Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

