


B 52035
QUICK FLOW® Plus thin sheet screw
 Form F | flanged button head | hexalobular drive

Steel | zinc-plated, thick-film passivated (VZD) | Cr(VI)-free | self-tapping thread
Incl. 3 suitable bits per PU



Diameter (d)	a max.	c max.	d ₁ nominal size	d ₂		e nominal size	k max.	r ₂ nominal size	Pitch (P)	t		Tool size
4	1	1.10	7.3	min.	max.	7	3.1	15	1.4	max.	min.	TX 20
5	1	1.35	9.2	10.8	11.5	9	3.7	30	1.6	1.91	1.52	TX 25

Length (l)	
nominal size	
	12
	19
	22

Diameter (d)	Length (l)		
	12	19	22
4	●	●	
5			●

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm