


DIN 966 similar to ISO 7047

Raised countersunk head screws

Cross-slot phillips

Stainless steel A2 | Cr(VI)-free | Metric thread

Further information: DIN standard has been withdrawn



Diameter (d)	a max.	dk		f	k max.	m	rf	r max.	Pitch (P)	Tool size
		min.	max.							
M2.5	0.9	4.40	4.7	0.60	1.50	2.7	5	0.7	0.45	H1
M3	1.0	5.30	5.6	0.75	1.65	3.1	6	0.8	0.50	H1
M4	1.4	7.14	7.5	1.00	2.20	4.5	8	1.0	0.70	H2
M5	1.6	8.84	9.2	1.25	2.50	5.3	10	1.3	0.80	H2
M6	2.0	10.57	11.0	1.50	3.00	6.8	12	1.6	1.00	H3
M8	2.5	14.07	14.5	2.00	4.00	9.0	16	2.0	1.25	H4

nominal size	Length (l)	
	min.	max.
5	4.75	5.25
6	5.75	6.25
8	7.70	8.30
10	9.70	10.30
12	11.65	12.35
14	13.65	14.35
16	15.65	16.35
18	17.65	18.35
20	19.60	20.40
25	24.60	25.40

nominal size	Length (l)	
	min.	max.
30	29.60	30.40
35	34.50	35.50
40	39.50	40.50
45	44.50	45.50
50	49.50	50.50
60	59.00	61.00
70	69.00	71.00

All technical data refer to the measure mm



DIN 966 similar to ISO 7047

Raised countersunk head screws

Cross-slot phillips

Stainless steel A2 | Cr(VI)-free | Metric thread

Diameter (d)	Length (l)																
	5	6	8	10	12	14	16	18	20	25	30	35	40	45	50	60	70
M2.5		●	●	●	●		●										
M3	●	●	●	●	●	●	●	●	●	●	●						
M4		●	●	●	●	●	●	●	●	●	●	●	●	●	●		
M5		●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
M6			●	●	●		●		●	●	●	●	●	●	●		
M8									●	●	●	●	●	●			

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

