

HELICOIL® manual taps

Type 0140.0 | Metric standard and fine thread

Short machine tap to create a holding thread (acc. to DIN 8140-2) for HELICOIL® coil thread inserts.



Properties:

- For through holes
- For blind holes (only if sufficient chip space is provided)
- Machining of materials with 700 N/mm² strength max.
- Tolerance class 6H mod. corresponds with 5H

Note:

Only suited for blind holes if sufficient chip space is provided. Minimum requirement: 1 d deeper than the full thread length.

The short machine tap can also be used as a machine tap.

Technical information can be found on the last page.

Diameter (d)	Article number	Version	Pitch (P)	D _{HC} min.	d ₂ nominal size	d ₃ nominal size	d ₄	L ₁	L ₂	L ₃	L ₄	K
M 2	01400020104	A	0.40	2.5	2.8	2	–	40	9	5	–	2.1
M 2.5	01400250104	B	0.45	3.1	3.5	2.5	2.6	40	10	6	13.5	2.7
M 3	01400030104	B	0.50	3.6	4	3	3.1	45	10	6	13.5	3.0
M 3.5	01400350104	B	0.60	4.3	4.5	3.5	3.6	45	12	6	15.5	3.4
M 4	01400040104	B	0.70	4.9	6	4	4.2	50	14	8	17.5	4.9
M 5	01400050104	B	0.80	6.0	6	5	5.2	50	16	8	19.5	4.9
M 6	01400060104	C	1.00	7.3	6	6	–	56	19	8	–	4.9
M 7	01400070104	C	1.00	8.3	7	7	–	63	19	8	–	5.5
M 8	01400080104	C	1.25	9.6	7	8	–	70	22	8	–	5.5
M 8x1	01400083104	C	1.00	9.3	7	8	–	63	19	8	–	5.5
M 9	01400090104	C	1.25	10.6	8	9	–	70	24	9	–	6.2
M 10	01400100104	C	1.50	11.9	9	10	–	75	27	10	–	7.0
M 10x1	01400103104	C	1.00	11.3	9	10	–	70	22	10	–	7.0
M 10x1.25	01400109104	C	1.25	11.6	10	9	–	70	22	10	–	7.0
M 11	01400110104	C	1.50	12.9	11	11	–	70	22	12	–	9.0
M 12	01400120104	C	1.75	14.3	11	12	–	80	30	12	–	9.0
M 12x1	01400123104	C	1.00	13.3	11	12	–	70	22	12	–	9.0
M 12x1.25	01400129104	C	1.25	13.6	11	12	–	70	22	12	–	9.0
M 12x1.5	01400124104	C	1.50	14.0	11	12	–	70	22	12	–	9.0
M 14	01400140104	C	2.00	16.6	12	14	–	80	32	12	–	9.0
M 14x1	01400143104	C	1.00	15.3	12	14	–	70	22	12	–	9.0
M 14x1.25	01400149104	C	1.25	15.6	12	14	–	70	22	12	–	9.0
M 14x1.5	01400144104	C	1.50	16.0	12	14	–	70	22	12	–	9.0
M 16	01400160104	C	2.00	18.6	14	16	–	80	22	14	–	11.0
M 16x1.5	01400164104	C	1.50	18.0	14	16	–	80	22	14	–	11.0
M 18x1.5	01400184104	C	1.50	20.0	16	18	–	80	22	15	–	12.0
M 18x2	01400185104	C	2.00	20.6	16	18	–	80	22	15	–	12.0
M 20x1.5	01400204104	C	1.50	22.0	18	20	–	80	22	17	–	14.5
M 20x2	01400205104	C	2.00	22.6	18	20	–	80	22	17	–	14.5
M 22x1.5	01400224104	C	1.50	24.0	18	22	–	90	22	17	–	14.5

All technical data refer to the measure mm



HELICOIL® manual taps


Type 0140.0 | Metric standard and fine thread

Diameter (d)	Article number	Version	Pitch (P)	D _{HC} min.	d ₂ nominal size	d ₃ nominal size	d ₄	L ₁	L ₂	L ₃	L ₄	K
M 22x2	01400225104	C	2.00	24.6	18	22	–	90	22	17	–	14.5
M 24x1.5	01400244104	C	1.50	26.0	18	24	–	90	22	17	–	14.5
M 24x2	01400245104	C	2.00	26.6	20	24	–	90	22	19	–	16.0
M 26x1.5	01400264104	C	1.50	28.0	20	26	–	90	22	19	–	16.0
M 27x1.5	01400274104	C	1.50	29.0	22	27	–	90	22	21	–	18.0
M 27x2	01400275104	C	2.00	29.6	22	27	–	90	22	21	–	18.0
M 28x1.5	01400284104	C	1.50	30.0	22	28	–	90	22	21	–	18.0
M 30x1.5	01400304104	C	1.50	32.0	22	30	–	90	22	21	–	18.0
M 30x2	01400305104	C	2.00	32.6	25	30	–	100	22	23	–	20.0
M 33x2	01400335104	C	2.00	35.6	28	33	–	125	40	25	–	22.0
M 36x1.5	01400364104	C	1.50	38.0	28	36	–	100	25	25	–	22.0
M 36x2	01400365104	C	2.00	38.6	32	36	–	125	40	27	–	24.0
M 36x3	01400366104	C	3.00	39.9	32	36	–	125	40	27	–	24.0

All technical data refer to the measure mm




HELICOIL® Plus thread inserts






W and d₁ are the control values for thread inserts (Free Running and Screwlock) before they have been installed. The length can only be measured for installed thread inserts.

Holding thread



Assembly



Prior to tapping, counter-bore 90° and deburr.
Outside diameter of countersink = $D_{HC} + 0.1 \text{ mm}$.

- | | |
|--|---|
| d = Nominal thread diameter | t ₁ = Minimum depth of tapped hole according to DIN 76 – Part 1 (guide value) |
| P = Thread pitch | t ₂ = The nominal length of the thread insert corresponds to the minimum length of the full parent thread for blind holes or the minimum plate thickness for a through hole. |
| d ₁ = Outside diameter of thread insert prior to installation | t ₃ = Maximum screw-in depth when the tang is not removed |
| W = Number of threads prior to installation | t ₅ = Distance of the thread insert from the joint face = 0.25 to 0.5 P, if t ₂ corresponds to the above-mentioned minimum value |
| D _{HC} = Outside diameter of the parent thread | |
| D _{1HC} = Crest diameter | |
| B = Suitable twist drill diameter. Please note: D _{1HC} is critical for selecting the correct twist drill diameter. | |

When you use HELICOIL® Plus thread inserts for volume production, we recommend to add at least 1 x P to values t₁ and t₂.

All technical data refer to the measure mm

