

HELICOIL® Tangfree installation mandrels with depth stop

for HELICOIL® Tangfree Free Running

HELICOIL® Tangfree installation mandrel to process HELICOIL® Tangfree Free Running coil thread inserts with UNF thread. Compatible with the hexagon socket of HELICOIL® Plus installation tools.



Suited for:

- E-S 206 and E-S 410 electrical installation tools
- P-S 412 and P-S 1216 pneumatic installation tools

Properties:

- 1/4" hex drive
- With depth stop

Delivery scope:

- Installation mandrel
- Telescopic sleeve
- Tool for blade change
- Operating instructions
- Packaging

Technical information can be found on the last page.

Diameter (d)	Article number	Pitch (P)	Nominal length t ₂
UNF 10-32	51604369700	0.79	4.8

All technical data refer to the measure mm



HELICOIL® Plus thread inserts





W and d_1 are the control values for thread inserts (Free Running and Screwlock) before they have been installed. The length can only be measured for installed thread inserts.

Holding thread



Assembly



tang not broken off

Prior to tapping, counter-bore 90° and deburr.
Outside diameter of countersink = $D_{HC} + 0.1 \text{ mm}$.

- d = Nominal thread diameter
- P = Thread pitch
- d_1 = Outside diameter of thread insert prior to installation
- W = Number of threads prior to installation
- D_{HC} = Outside diameter of the parent thread
- D_{1HC} = Crest diameter
- B = Suitable twist drill diameter. Please note: D_{1HC} is critical for selecting the correct twist drill diameter.
- t_1 = Minimum depth of tapped hole according to DIN 76 – Part 1 (guide value)
- t_2 = The nominal length of the thread insert corresponds to the minimum length of the full parent thread for blind holes or the minimum plate thickness for a through hole.
- t_3 = Maximum screw-in depth when the tang is not removed
- t_5 = Distance of the thread insert from the joint face = 0.25 to 0.5 P, if t_2 corresponds to the above-mentioned minimum value

When you use HELICOIL® Plus thread inserts for volume production, we recommend to add at least $1 \times P$ to values t_1 and t_2 .

All technical data refer to the measure mm

