## **ISO 4017** similar to DIN 933

## **Hexagon head bolts**


Hexagon head | fully threaded

Steel 8.8 | zinc-plated | Cr(VI)-free | Metric thread

Further information: DIN-standard has been withdrawn  $\mid$  changed spanner widths for M10, M12, M14 and M22

There is a separation into product classes A and B, with the data sheet showing the largest range of values. For more information, see the technical details of the selected article.







Diameter	á	a	(		da	d <sub>w</sub>	е		k		r			Pitch
(d)	min.	max.	min.	max.	max.	min.	min.	nominal size	min.	max.	min.	max.	min.	(P)
M4	0.70	2.1	0.15	0.4	4.7	5.74	7.50	2.8	2.68	2.92	0.2	7	6.64	0.70
M10	1.50	4.5	0.15	0.6	11.2	14.47	17.59	6.4	6.11	6.69	0.4	16	15.57	1.50
M12	1.75	5.3	0.15	0.6	13.7	16.47	19.85	7.5	7.21	7.79	0.6	18	17.57	1.75
M16	2.00	6.0	0.20	0.8	17.7	22.00	26.17	10.0	9.82	10.18	0.6	24	23.16	2.00

Length (I)							
nominal size	min.	max.					
12	11.65	12.35					
20	18.95	21.05					
22	20.95	23.05					
25	23.95	26.05					
27	25.95	28.05					
28	26.95	29.05					
30	28.95	31.05					
35	33.75	36.25					

Length (I)						
nominal size	min.	max.				
40	38.75	41.25				
45	43.75	46.25				
50	48.75	51.25				
55	53.50	56.50				
60	58.50	61.50				
65	63.50	66.50				
70	68.50	71.50				
75	73.50	76.50				

Length (I)							
nominal size	min.	max.					
80	78.50	81.50					
85	83.50	86.50					
90	88.25	91.75					
95	93.25	96.75					
100	98.25	101.75					
110	108.25	111.75					
120	118.25	121.75					
170	168.00	172.00					


## All technical data refer to the measure mm

**ISO 4017** similar to DIN 933

## **Hexagon head bolts**

Hexagon head | fully threaded

Steel 8.8 | zinc-plated | Cr(VI)-free | Metric thread



• Combinations available in the eShop | Other sizes on request