

## RIVKLE® Standard blind rivet nuts

Stainless steel | Flat head | Semi-hexagonal | Hexagonal | Closed

Note: RIVKLE® produced in stainless steel for an optimal corrosion resistance | Thread according to ISO 6h (ISO 68-1)


Technical information can be found on the last page.




Diameter (d)	Article number	Drilling diameter d nominal size	B	E nominal size	L <sub>2</sub>	e		Length (l) nominal size	S
						min.	max.		
M 3	23358030023	5	7	0.7	9.2	1.1	2.3	12.7	S = 3.8 - e
	23358030030	5	7	0.7	9.5	2.3	3.0	14.3	S = 4.5 - e
M 4	23358040020	6	8	0.8	11.5	0.5	2.0	15.5	S = 3.8 - e
	23358040040	6	8	0.8	11.5	2.0	3.5	17.5	S = 5.6 - e
M 5	23358050001	7	9	1	12.5	0.5	3.0	19.6	S = 5.0 - e
	23358050040	7	9	0.8	13.5	2.0	4.0	20.0	S = 6.1 - e
M 6	23358060030	9.1	12	1.5	15.5	0.5	3.0	22.3	S = 4.0 - e
	23358060045	9	11	1.4	15.5	3.0	4.5	23.7	S = 7.1 - e
M 8	23358080001	11	14	1.5	19.5	0.8	3.0	26.1	S = 5.3 - e
	23358080055	11	14	1.4	18.0	3.0	5.5	27.0	S = 8.2 - e
M 10	23358100035	13	16	1.8	27.5	1.0	3.5	31.5	S = 7.4 - e
	23358100055	13	16	1.8	27.5	3.5	5.5	33.5	S = 9.4 - e

All technical data refer to the measure mm






**Head diameter**  
**Overall length**  
**Thread size**



**Grip range**  
 Defines the range of total thickness of the customers part (even if it consists of more than one layer)



**Hole geometry**  
 If round → diameter  
 If hexagonal → width across flats




**Head projection after setting**  
 Variable according to the application (setting load, material substrate, etc.)

**Blind side projection after installation**  
 Defines the clearance needed on the blind side (cannot be used for quality control)

**Setting stroke**  
 Difference of total length before and after installation

**RIVKLE® Nut**



**RIVKLE® Stud**



- RIVKLE®
- Mandrel\*
- Customers part
- Anvil\*
- Counter nut
- Setting tool

\*in accordance to chosen RIVKLE®\*

All technical data refer to the measure mm

