

## RIVKLE® PNC Standard blind rivet nuts

Stainless Steel | Flat head | Slotted | Cylindrical | Open

Note: need specific mandrel (longer)

Technical information can be found on the last page.



Diameter (d)	Article number	Drilling diameter d		B	D	E nominal size	L <sub>2</sub>	e		Length (l) nominal size
		min.	max.					min.	max.	
M 4	66830488038	6.13	6.25	11.1	6.12	0.96	8.6	0.50	3.80	17.61
M 5	66830588044	7.48	7.58	12.7	7.47	0.95	9.9	0.50	4.45	22.00
	66830588081				7.97			4.45	8.10	24.77
M 6	66830688071	8.80	8.90	15.9	8.79	1.5	12.8	0.50	7.10	26.87
	66830688127				8.79			7.10	12.70	32.79
M 8	66830888071	11.11	11.50	19.0	11.10	1.5	14.5	0.50	7.10	30.50
M 10	66831088071	13.07	13.26	22.2	13.06	2.24	15.8	0.50	7.10	33.17

All technical data refer to the measure mm





**Head diameter**  
**Overall length**  
**Thread size**




**Grip range**

Defines the range of total thickness of the customers part (even if it consists of more than one layer)



**Hole geometry**

If round → diameter  
 If hexagonal → width across flats



**Head projection after setting**

Variable according to the application (setting load, material substrate, etc.)

**Blind side projection after installation**

Defines the clearance needed on the blind side (cannot be used for quality control)

**Setting stroke**

Difference of total length before and after installation

**RIVKLE® Nut**



**RIVKLE® Stud**



- RIVKLE®
- Mandrel\*
- Customers part
- Anvil\*
- Counter nut
- Setting tool

\*in accordance to chosen RIVKLE®\*

All technical data refer to the measure mm

